

## GKF-30 Oven with Digital Thermostat (30 Packages)

- Electrodes are subjected to shocks after being kept at 300°C for 2 hours. The then the electrodes is kept in thermostat lowered to 130°C
- It is used for subjecting to a shock after keeping them at a high temperature and preserving their heat at a low temperature for drying process



### General Data

Capacity	3000bar
Height (y)	113-80cm
External Diameter (g)	64x67cm
Internal Diameter	30x50x66cm
Tray Dimensions and Quantity	38x47x7cm / 3 trays
Max Heating Temperature	0-400°C
Heat Control	Digitally Controlled
Operating Capacity	4500W
Operating Voltage	380-400V
Operating Current	21A
Heat Insulation	Available
Weight	110kg

### Standard and Optional Equipment

6051700007

This Order Code Relates to All Equipment

## GKF-50 Oven with Digital Thermostat (50 Packages)

- Electrodes are subjected to shocks after being kept at 300°C for 2 hours. The thermostat is then lowered to 130°C, and electrodes are not subjected to any further treatment.
- It is used for subjecting to a shock after keeping them at a high temperature and preserving their heat at a low temperature for drying process.



### General Data

Capacity	5000bar
Height (y)	150x115cm
External Diameter (g)	67x77cm
Internal Diameter	23x50x96cm
Tray Dimensions and Quantity	22x45x7cm / 10 trays
Max Heating Temperature	0-400°C
Heat Control	Digitally Controlled
Operating Capacity	4500W
Operating Voltage	380-400V
Operating Current	21A
Heat Insulation	Available
Weight	160kg

### Standard and Optional Equipment

6051700008

This Order Code Relates to All Equipment